

# Freeze Capture

Page 1 of 1

9 Jan 2017 10:46

## Key Parameters

Mode	DDD
Base Rate	60 bpm
Rest Rate	50 bpm
Paced AV Delay	180 ms
Sensed AV Delay	100 ms
Max Track Rate	150 bpm
Max Sensor Rate	125 bpm
Hysteresis Rate	Off
ACap™ Confirm	Off
V. AutoCapture	Off
AF Suppression™	Off
Ventricular Intrinsic Preference (VIP™)	On
Negative AV Hysteresis/Search	Off
Rate Responsive AV Delay	Off
Rate Responsive PVARP/V Ref	High
Ventricular Safety Standby	On

1: II AutoGain (8.7 mm/mV)

4: A Sense Amp AutoGain (1.7 mm/mV)

2: I AutoGain (13.8 mm/mV)

5: V Sense Amp AutoGain (2.3 mm/mV)

3: Markers

Sweep Speed: 25 mm/s

